






QUICKTRONIC® FIT T5/T8

	QT-FIT5/8 1x18-39	QT-FIT5/8 1x54-58	QT-FIT5/8 2x18-39	QT-FIT5/8 2x54-58
10A (B) 	17 x 	17 x 	12 x 	8 x 
16A (B/C) 	28 / 47 x 	28 / 47 x 	19 / 32 x 	13/ 22 x 
	≤ 24 A	≤ 24 A	≤ 40 A	≤ 53 A
TH	230 μs	230 μs	200 μs	200 μs


QT-FIT 5/8 1x...



Max. permitted cable length in between ECG and lamp: 2.0 m (PIN 21, 22); 1.0 m (PIN 23, 24)

QT-FIT 5/8 2x...

Max. permitted cable length in between ECG and lamp: 2.0 m (PIN 21, 22); 1.5 m (PIN 23, 24); 1.0 m (PIN 25, 26)



- (D) Max. Leitungslänge zwischen EVG und Lampe; Leitungslänge max.
- (RUS) Максимально допустимая длина кабеля между ЭПРА и лампой
- (KZ) Құрылғы мен шам арасындағы кабельдің максималды ұзындығы

